




STANDARD PRODUCT PORTFOLIO

COMPRESSION CONTACT TECHNOLOGY

STACKERS | BOARD-TO-BOARD



KEY FEATURES:

- Highly reliable, fatique resistant, gold plated Beryllium Copper contacts
- Enhanced deflection capabilities to absorb assembly tolerances
- Maximized contact forces to meet high reliability / harsh environments applications
- One-Piece Connector used to connect two PCBs in a cost effective manner

PARALLEL/ STACKING APPLICATIONS	Tall Stacker 9148-000	Dual Row Stacker 9158-000	Staggered Stacker 9188-000	Ultra-Low Profile Stacker 9258-000
		The state of the s	The State of the S	THITTING THITTING
Pitch	1.0mm	1.0mm	1.0mm	1.0mm
# of Positions	8	16, 20, 24, 28, 32 *(30, 40, 18)	4, 6, 8	8
Compressed / Working Height from PCB Surface	8mm	1.9mm to 3.3mm *(3.9mm to 5.1mm)	1.1mm to 1.3mm (4P) 1.9mm to 2.1mm (4, 6, 8P)	0.4mm & 0.8mm
Deflection Force	27g to 35g	20g to 41g	36g to 52g	32g to 52g
Current Rating	1A/contact	1A/contact	1A/contact	1A/contact
Durability	50 cycles	50 cycles	50 cycles	50 cycles

^{*}Special product variations, please contact KAVX for more information

