



Energy Bank Capacitor Applications





I. INTRODUCTION

II. ELECTRICAL PARAMETERS

- > Energy
- > Peak current (discharge voltage)
- > Voltage ripple
- > Pulse Current
 - > Principle
 - > Pulse Forming Network

III. AVX REALIZATIONS

- > AVX Knows How
- DC filtering for industrial application
 - > Reasonance filters for railways substations
 - > DC filter for power electronic tube
- > Pulse Forming Network for HIgh Power LASER
- > DC Energy storage for 50/60Hz converter
- > DC Energy storage for Smoother filter
- > DC Energy storage for Power System Booster
- > Discharge Energy Bank for Electromagnetic gun

IV. GUIDE FOR CUSTOMER'S SPECIFIC REQUIREMENTS



INTRODUCTION

High Power capacitors can be identified as storage volume. A tank will storage water drop, capacitors will storage electrical charge (electrons).

Everybody knows what is a dam or flood barrier or a toilet flush, Energy Storage Capacitor will act as dam or toilet flush

The principle of working is a "long" charge time and a "short" discharge time in order to generate a short pulse with peak current

Short pulse with peak current will produce a high power pulse able to create :

- high magnetic field in inductances
- or magnetic field in magnets
- or an ionization in a lamp
- or a plasma in the material
- or EM pulse lightning
- or High Frequency tubes

Applications are multiples but some of them are well identified as :

- Particles accelerators in Research Labs
- EM guns for Military applications
- Fusion Laser for Military applications
- High Magnetic field for research (Medical)
- Marx Generator for Military applications and Electrical Labs
- EM cylinders
- Electrical Forming
- Klystrons and other High Power electronic tubes

Some others classical applications DC banks filtering in storage High Energy application are met for Transport&Distribution of Energy (Flexible AC Transmission System, STAtic COMpensator, Unified Power Flow Controller).

More and more, banks of capacitors are used as Energy storage banks in order to deliver energy during several 100ms. Contrary to batteries and supercapacitors, power capacitors have no limitation in term of discharge time.

These High Energy applications request not only few elementary capacitors but lot of capacitors mechanical mounted and electrical connected on mechanical frames.



ELECTRICAL PARAMETERS



II.1. Energy

Power range means several kV and "High" capacitance in order to generate "High" energy from 100kJ up to several MJ per equipment. The max elementary capacitance is about 125kJ per unit.

We remember that : Energy = $\frac{1}{2}$ CV² (with E in Joule, C in F and V in Volt).

II.2. Peak Current (discharge voltage)

If Peak Current is proportional to capacitance, current depends also of ratio between voltage and time of discharge. Depending of applications, Peak Current can shift from few kA up to several MA.

We remember that :

Ipeak = $C \Delta V / \Delta t$ (with Ipeak in Amps, C in F, V in Volt and t in second)

An example for energy bank C=10x300µF/24kV







ELECTRICAL PARAMETERS

II.3. Voltage Ripple



The energy bank will discharge itself partially about 80% during 500ms. This discharge can be repeat several times per day or few times per month.

The target is to present energy storage available in case of switching or short time disruption. In this case batteries or supercapacitors cannot provide this energy during this time, electrolytic caps cannot be used due to high voltage and high energy and security of working.

II.4. Pulse Current

II.4.1. Principle

Capacitor (C) charge or discharge is first order mode, exponential law in serial resistance (R). If in the circuit we add an inductance (L), at minimum there is always inductance due to serial inductance of cap and inductance of connections, the charge and discharge mode will be second order with sine waves of current and voltage.





ELECTRICAL PARAMETERS



A R, L, C circuit can generate only sine waves pulse but sometimes, the load request square pulses, it's the case of magnetron, klystron or magnets.

In this case it's necessary to use a PFN (Pulse Forming Network).



II.4.2. Pulse Forming Network

A PFN, is realized with L, C cells, same as delay line, but the PFN is charge and discharged in its entrance on its characteristic impedance in order to generate a square calibrated pulse without reversal. Square pulse have specific characteristics as : rise time, fall time, overshoot, ripple, ramp that AVX control with cells characteristics. AVX is a the only one company to design and to manufacture PFN.





III. AVX realizations

III.1. AVX Knows How

AVX has more 47 years of experience in electrotechnic field, the usual values are kilo Volt x kilo Amps = Mega Watt. Size of such applications induce several m3 and several tons. AVX Know How is to design such components meeting electrical and mechanical functions. AVX is also able to design mechanical s tructure supporting capacitors, electrical insulation, connections and cabling.

III.2. DC filtering for industrial application

Depending of power application, when one reach several MW, several DC capacitors are connected in parallel.

III.2.1. Resonance filter for railways substations



C2943 : 2175µF +/- 2% - 6.2kV - 220kg





III.2.2. DC filter for power electronic tube



TFL 118 : 160 μ F +/- 10% - 32kV – 1250kg



 $L1296: 500 \mu s - 58 kV - 1.5 MW - 23000 kg$



III.4. DC Energy storage for 50/60Hz converter



C2961 : 74000µF +/- 5% - 4.2kV - 4500kg

Nota : Total bank per converter is 0.28F/4.2kV





III.5. DC Energy storage for Smooth filter for electromagnets (Synchrotron Power Supply)





C2953 : 400.000µF +/-5% - 1650 V - 1500kg

- Nota : these cabinets have been designed and realized with additional control/command functions as :
- Thermal measurements
- Zero Voltage Testing
- Security system
- Programmable Logic Computer



III.6. DC Energy storage for Power System Booster for Magnets supply for Proton Synchrotron



C2955 : 64575µF +/- 2.5% - 5kVdc - 3450kg



Nota : the total bank is 0.25F / 5kVdc working in marine containers



III.7. Discharge Energy Bank for Electromagnetic gun (Military applications)



C2931: 0.17F +/- 10% - 10.75kV - 29000kg





CUSTOMER'S SPECIFIC REQUIREMENTS

| Company / Name / Email / Phone | | | Project / Quantity | |
|--|-----------|-----------------------|--------------------|--|
| | | | | |
| | | | | |
| Applications | DC Applie | Discharge Application | | |
| Total Capacitance (µF) | | | | |
| Tolerance (%) | | | | |
| Operating coltage (ripple included) | | | | |
| Ripple voltage (peak to peak) | | | | |
| Working frequency (Hz) | | | | |
| Peak current | | | | |
| RM S current | | | | |
| M aximum current/duration | | | | |
| Discharge | | | | |
| Pulse duration @ 5%lpeak (µs) | | | | |
| Time to Ipeak (µs) | | | | |
| Ringing Frequency (Hz) | | | | |
| Reversal Voltage (%) | | | | |
| Repetition rate | | | | |
| Hold time @ full voltage (s) | | | | |
| Fault peak current/nb shots | | | | |
| Fault reversal voltage (%) | | | | |
| Lifetime expectancy | | | | |
| Maximum Inductance (nH) | | | | |
| Test voltage between terminals (kV) | | | | |
| Test voltage between shorted terminals and case (kV) | | | | |
| Maximum surge voltage M SV (kV) | | | | |
| M SV Duration / Frequency | second | /year | | |

| Capacitors Integration | | | | | | | |
|----------------------------|-------|-----------------------------|------------|--------------|--------|--|--|
| Capacitors Dimensions (mm) | | Operating Position | Terminals | | | | |
| length | width | hight | vertical | Туре | Number | | |
| | | | horizontal | | | | |
| Bank Information | | | | | | | |
| Bank available volume (mm) | | Insulation level (k V rm s) | | | | | |
| length | width | hight | form0V | fromg ground | | | |
| | | | | | | | |

| Thermal Characteristics | | | | | | |
|---|---------|--------------------|--|--|--|--|
| Storage temperature (°C) Operating Temperature (°C) | | Cooling | | | | |
| min | min | Natural Convection | | | | |
| average | Average | Foreced Air | | | | |
| max | max | | | | | |

Remarks



ABOUT KYOCERA AVX

KYOCERA AVX is a worldwide leading supplier of passive electronic components, connectors, passive and active antennas, sensors and control units. KYOCERA AVX offers a wide range of components manufactured to the highest quality and reliability standards.

Our products include ceramic, solid electrolytic and film capacitors, pulse supercapacitors, varistors, thermistors, filters, inductors, diodes, antennas, connectors, sensors and control units. Our worldwide manufacturing capability includes facilities located in seventeen countries on four continents, allowing us to continue meeting customer needs on a global basis. KYOCERA AVX is committed to supporting the needs of its customers for applications today and in the future. Together with continuous quality improvement process, KYOCERA AVX components provide reliable solutions for consumer application needs.

As a technology leader, KYOCERA AVX will continue to add to its product portfolio on a regular basis. Details of new devices being offered and their specifications will be shown on the KYOCERA AVX website: WWW.KYOCERA-AVX.COM.

