



# ethertronics<sup>®</sup>

AN **AVIX**<sup>®</sup> GROUP COMPANY

---

## **Application Note 005**

**Active Steering MCD Algorithm  
Test Result for ETH-LORA-M-AX-01 (V1.2)**

# Table of Contents

---

<b>Overview</b> .....	1
Requirement.....	1
Scope .....	1
<b>General Description</b> .....	1
MCD Algorithm.....	1
Active Evaluation Board .....	2
Setup Condition .....	3
Gain Measurement Setup .....	3
RSSI Measurement Setup.....	3
<b>Result</b> .....	4
Antenna Gain Measurement (Passive Tests) .....	4
RSSI measurement (Active tests).....	5
Position 1 .....	5
Position 2.....	7
<b>Conclusion</b> .....	9

# Application Note 005

## Active Steering MCD Algorithm Test Result for ETH-LORA-M-AX-01 (V1.2)

### OVERVIEW

The Ethertronics LoRa module ETH-LORA-M-AX-01 (V1.2) embeds two antenna RF technology to maximize antenna performances:

- Closed loop Impedance Matching (IM) to maximize the power transferred to the antenna when the antenna is detuned by its environment.
- Active Steering Technologies to maximize link connectivity. With that feature, the radiation pattern of the active steering antenna is driven by Ethertronics Modal Cognitive Diversity (MCD) algorithm in order to enhance RF budget link and increase reliability and range.

The purpose of this document is to show the result of the active steering MCD technology embedded in the module ETH-LORA-M-AX-01 (V1.2).

This document is divided in the following parts:

- General description
- MCD Result
- Conclusion

### REQUIREMENT

To perform the test of the MCD algorithm the items below are needed.

#### Hardware Tools:

1. EtherLoRa module ETH-LORA-M-AX-01 (V1.2).
2. USB-UART Cable (FTDI USB-UART TTL Cable)
3. Computer with Windows OS
4. LoRa Gateway
5. Vector Network Analyzer (VNA)
6. Anechoic chamber

#### Software Tools:

1. Driver for USB-UART cable
2. Ethertronics EtherLoRa ETH-LORA-M-AX-01 Control Tool

### SCOPE

This document focuses on the active steering technology (and its' algorithm, MCD). This algorithm is running independently of the other RF technology (Closed Loop Impedance Matching (IM) algorithm) and but can only be used with an active steering antenna in active configuration of this module. In this document, an embedded active steering PCB antenna is used.

### GENERAL DESCRIPTION

#### MCD ALGORITHM

The active steering algorithm MCD is developed by Ethertronics to perform active steering capabilities of the multi radiation patterns antenna in order to improve the link budget and sensitivity. In addition, the interference to the neighbour devices can be reduced when the gain of the antenna is steered to the right direction (LoRa gateway). The MCD algorithm predicts the the best antenna configuration for the next data packet in order to optimize the LoRa communication and data transmission rate.

#### BLOCK DIAGRAM OF THE MODULE USED WITH AN ETHERTRONICS ACTIVE STEERING ANTENNA




Figure 1

# Application Note 005

## Active Steering MCD Algorithm Test Result for ETH-LORA-M-AX-01 (V1.2)

### ACTIVE EVALUATION BOARD

To facilitate the final product developers, Ethertronics has built a completed active evaluation board (EVB) for ETH-LORA-M-AX-01 (V1.2). In order to test the functionalities of the MCD algorithm, an active evaluation board is used. This evaluation board comes with test connectors to communicate with ETH-LORA-M-AX-01 using AT commands via UART interface. This board is also provided with Ethertronics' Active Steering antenna for ISM Band which covers the LoRa frequencies (868/915 MHz).

#### ACTIVE EVB (TOP VIEW)



Figure 2

#### ACTIVE EVB (BOTTOM VIEW)




Figure 3

#### ACTIVE EVB COMPONENTS

Component	Position	Function	Description
ETH-LORA-M-AX-01	Top	LoRa Module	Module to communicate LoRa communication
Active Steering PCB Antenna	Top	Active Antenna with EC686	Emit/receive the signal
Push Button	Top	Reset button	Reset the ETH-LORA-M-AX-01
Test connectors 1	Top	UART/Power Supply	To communicate using AT Commands and to supply the voltage to the module
Test connectors 2	Top	EC686 MIPI interface	To communicate directly with the external EC686 via MIPI interface
Toggle switch	Top	Power Supply selection	To select the power supply whether from Battery or Test connector
Battery holder	Bottom	Place for 3 AA batteries	To supply the voltage to the module

Table 1

For more information about the active evaluation board, please refer to LoRa\_Module\_Application\_Note\_4-Active Steering Evaluation Board document from [www.avx.com/products/modules/lora-module](http://www.avx.com/products/modules/lora-module).

# Application Note 005

## Active Steering MCD Algorithm

### Test Result for ETH-LORA-M-AX-01 (V1.2)

#### SETUP CONDITION

The measurement has been done for LoRa EU-868 band. In the first phase the measurement of gain of the active steering PCB antenna has been done. Based on the result of the first phase, two positions are created to evaluate the MCD algorithm.

#### GAIN MEASUREMENT SETUP




Figure 4

For the gain measurement, the active EVB is modified to connect the RF cable on the PCB. The device is then measured inside Ethertronics' anechoic chamber. Using Ethertronics' measurement and post processing software installed on the PC, the gain measurement is obtained.

- The measurement software controls the motors inside the chamber and also controls the VNA.
- The post processing software calculates the gain based on the values retrieved from the VNA.

#### RSSI MEASUREMENT SETUP




Figure 5

The control software is installed on the PC host. User can use this software to communicate with the module ETH-LORA-M-AX-01 using AT commands. The procedures are as follow:

1. Setup the MCD algorithm parameters if necessary
2. Initiate the join procedure using OTAA with gateway
3. Start the MCD algorithm
4. Start the listener to collect information necessary and the state of the algorithm
5. Send the message to the gateway every 20 seconds
6. For every response of the gateway, the information is logged for the post processing.

# Application Note 005

## Active Steering MCD Algorithm

### Test Result for ETH-LORA-M-AX-01 (V1.2)

## RESULT

### ANTENNA GAIN MEASUREMENT (PASSIVE TESTS)

The eval board ETH-LORA-M-AX-01 (V1.2) has a patented Ethertronics Active Steering antenna which can exhibit up to two modes, meaning three different radiation patterns.

Any of the two radiation pattern can be considered as equivalent to the radiation pattern of a typical passive antenna (mounted in different position).

The axes of the measurement are as follow:



### RADIATION PATTERNS FOR EU-ISM 868MHZ




Figure 6

# Application Note 005

## Active Steering MCD Algorithm Test Result for ETH-LORA-M-AX-01 (V1.2)

### RSSI MEASUREMENT (ACTIVE TESTS)

Active measurements with the LoRa module were performed in anechoic chamber equipped with a LoRa gateway. Active measurements with the LoRa module were performed with the EVB in two different positions.

#### POSITION 1

#### POSITIONING OF THE DEVICE AND THE GATEWAY IN POSITION 1 (TOP VIEW)




Figure 7

In this position, the mode 1 should be selected by the MCD algorithm because the mode 1 has a better gain than the mode 2 (see the blue curve of the gain pattern towards the gateway antenna in the picture above).

# Application Note 005

## Active Steering MCD Algorithm

### Test Result for ETH-LORA-M-AX-01 (V1.2)

#### RSSI AND MCD MODE IN POSITION 1




Figure 8

The MCD algorithm converges to mode 1 in the position 1. The RSSI measurement shows that the mode 1 has the better RSSI values and the MCD has selected the best mode.




# Application Note 005

## Active Steering MCD Algorithm

### Test Result for ETH-LORA-M-AX-01 (V1.2)

POSITION 2

POSITIONING OF THE DEVICE AND THE GATEWAY IN POSITION 2 (TOP VIEW)



# Application Note 005

## Active Steering MCD Algorithm

### Test Result for ETH-LORA-M-AX-01 (V1.2)

#### RSSI AND MCD MODE IN POSITION 2




Figure 10

# Application Note 005

## Active Steering MCD Algorithm Test Result for ETH-LORA-M-AX-01 (V1.2)

### CONCLUSION

From the passive tests:

- In position 1, the mode 1 has a better gain than the mode 2.
- In position 2, the mode 2 has a better gain than the mode 1.

### GAIN MEASUREMENT SUMMARY

	Description	Gain (XZ cut)
Position 1	Mode 1	~0dBi
	Mode 2	~-7dBi
	Achievable Improvement	~7dB
Position 2	Mode 1	~-4dBi
	Mode 2	~0dBi
	Achievable Improvement	~4dB

Table 2

From the active measurements with the module connected to the gateway, it appears that the MCD algorithm has always selected the best mode leading to the best RSSI value of each positions.

	Description	RSSI
Position 1	Mode 1	~-98.5dBm
	Mode 2	~-103dBm
	Achievable Improvement	~4.5dB
Position 2	Mode 1	~-105dBm
	Mode 2	~-103dBm
	Achievable Improvement	~2dB

Table 3

When changing between mode, the improvement, in that test, can reach up to 4.5dB

# Application Note 005

## Active Steering MCD Algorithm Test Result for ETH-LORA-M-AX-01 (V1.2)

### LIST OF ABBREVIATIONS

LoRa: Long range  
IM: Impedance Matching  
MCD: Modal Cognitive Diversity  
USB: Universal Serial Bus  
TTL: Transistor–transistor logic level  
UART: Universal Asynchronous Receiver/Transmitter  
OS: Operating System  
VNA: Vector Network Analyzer  
EU: European Union  
RF: Radio Frequency  
ISM: industrial, Scientific and Medical  
EVB: Evaluation Board  
OTAA: Over The Air Activation  
DUT: Device Under Test  
RSSI: Received Signal Strength Indicator

### LIST OF FIGURES

Figure 1: Block diagram of the module used with an Ethertronics Active Steering antenna .....	1
Figure 2: Active EVB (top view) .....	2
Figure 3: Active EVB (bottom view) .....	2
Figure 4: Polar Gain Measurement Setup.....	3
Figure 5: RSSI Measurement Setup .....	3
Figure 6: Radiation patterns for EU-ISM 868MHz .....	4
Figure 7: Positioning of the Device and the Gateway in Position 1 (top view).....	5
Figure 8: RSSI and MCD Mode in Position 1 .....	6
Figure 9: Positioning of the Device and the Gateway in Position 2 (top view).....	7
Figure 10: RSSI and MCD Mode in Position 2 .....	8

### LIST OF TABLES

Table 1: Active EVB components .....	2
Table 2: Gain Measurement Summary .....	9
Table 3: RSSI Measurement Summary .....	9



# ethertronics®

AN **AVXX** GROUP COMPANY

## Americas

+(1) 858.550.3820  
eth.usasales@avx.com

## Europe

+33 (0) 4 93 74 30 71  
eth.europesales@avx.com

## Asia

Korea: 82.31.436.2290  
China: 886.2.2655.7966

**FOLLOW US:**     

VISIT US AT [WWW.AVX.COM](http://WWW.AVX.COM) 